



Very-Low-Power IC for Capacitive Touch Sensor Solutions

October 25th, 2010 Document-No.: DB\_PCapØ1\_Touch\_en



#### Published by acam-messelectronic gmbh © copyright 2010 by acam-messelectronic gmbh, Stutensee, Germany

#### Legal note

The present data sheet is still under development, which may result in corrections, modifications or additions. acam cannot be held liable for any of its contents, neither for accuracy, nor for completeness. The compiled information is believed correct, though some errors and omissions are likely. We welcome any notification, which will be integrated in succeeding releases.

The acam recommendations are believed useful, the firmware proposals and the schematics operable, nevertheless it is of the customer's sole responsibility to modify, test and validate them before setting up any production process.

acam products are not designed for use in medical, nuclear, military, aircraft, spacecraft or lifesupport devices. Nor are they suitable for applications where failure may provoke injury to people or heavy material damage. acam declines any liability with respect to such non-intended use, which remains under the customer's sole responsibility and risk. Military, spatial and nuclear use subject to German export regulations.

acam do not warrant, and it is not implied that the information and/or practice presented here is free from patent, copyright or similar protection. All registered names and trademarks are mentioned for reference only and remain the property of their respective owners. The acam logo and the PicoCap logo are registered trademarks of acam-messelectronic gmbh, Germany.

#### Support / Contact

For a complete listing of direct sales contacts, distributors and sales representatives visit the acam website at:

http://www.acam.de/company/distributors.

For technical support you can contact the acam support team in the headquarter in Germany or the distributor in your country. The contact details of acam in Germany are:

sales@acam.de or by phone +49 7244 7419 O.

### **Table of Content**

1	System Overview	1-1
1.1	Features	1-1
1.2	Target Applications	1-1
1.3	Future Developments	1-1
2	Characteristics & Specifications	2-1
2.1	Electrical Characteristics	2-1
2.1.	1 Absolute Maximum Ratings	2-1
2.1.	2 Recommended Or Typical Operating Conditions	2-1
2.2	Converter Characteristics	2-1
2.3	Package Characteristics	2-2
2.3.	1 Mechanical	2-2
2.3.	2 Pin Outline	2-2
2.3.	3 Pin Assignment	2-3
2.3.	4 Recommended Schematics	2-4





### **1** System Overview

PCapØ1-Touch is a capacitive touch controller based on **BEAM**'s patented **PIED**CAP® principle. This entirely digital IC comes with adaptive algorithms, programmed ready-to-use in OTP memory and booting within microseconds after power-up.

The device consumes very little power.

#### 1.1 Features

- 6 capacitive touch sensors connectable
- 6 CMOS output ports that indicate touch state
- Digital measuring principle in CMOS technology
- Powerful filter functions integrated
- Asymmetric automatic drift compensation

- Simultaneous multiple key sensing
- Robustness against EMI
- Rapid response after status change (100 ms delay in average)
- Single power supply (2.1 to 3.6 V)
- Extremely low current consumption : 2 μA @ 3.0 V @ 6 Sensors

#### 1.2 Target Applications

- · Coin-cell and other battery-driven devices
- Remote Control Handsets
- Household Metering Devices
- Industrial Metering Devices
- White goods (household appliances)

#### **1.3 Possible Enhancements**

We are actively developing a different PCB layout and a modified firmware for matrix touch pads to control up to 28 touch-keys, with the same very low power consumption as above.





### 2 Characteristics & Specifications

#### 2.1 Electrical Characteristics

#### 2.1.1 Absolute Maximum Ratings

Supply voltage V <sub>DD</sub> -to-GND	- 0.3 to 4.0 V		
ESD rating (HBM), each pin	> 2 kV		
Storage temperature T <sub>stg</sub>	-55 to 150 °C		
Junction temperature (T <sub>j</sub> )	max. 125 °C		
OTP Data Retention Period (for the algorithms)	10 years at 95 °C temperature		

#### 2.1.2 Recommended Or Typical Operating Conditions

Parameter	Remarks	Min.	Тур.	Max.	Unit
Supply voltage $V_{\text{DD}}$		2.1		3.6	V
Operating current	at 2.1 volts and at scan speed 20 Hz per touch sensor		1.8		μA
	at 3.0 volts and at scan speed 20 Hz per touch sensor	0.9	2.0	2.5	μA
High-level output voltage	at the OLIT parts	V <sub>DD</sub> - 0.4 V			
Low-level output voltage				0.4 V	

#### 2.2 Converter Characteristics

Parameter	Remarks	Min.	Тур.	Max.	Unit
tolerated touch sensor capacitance		5	10	22000	рF
scan speed per touch sensor			20		S <sup>-1</sup>
switching delay			100		ms
time-out (individual for each sensor)	In case of a permanent change in capacitance		15		S
sensor protective coa- ting thickness	glass, acrylic sheet, other polymers		З		mm

### **PICO**CAP

#### 2.3 Package Characteristics

Figure 2-1: QFN-Dimensions



#### 2.3.1 Mechanical

	Dimensions in mm							
Package	D, E	D2, E2	N	е	L	b	Α	A3
QFN24	4.00	2.70	6	0.5	0.35	0.25	0.75/0.9	0.20

#### 2.3.2 Pin Outline



Note: (a) a dedicated, smaller housing with fewer pins is under study;

(b) the presently available housing is marked "PCapO1-AK" rather than "PCapO1-TOUCH"



#### 2.3.3 Pin Assignment

Mne- monic	Pin#	Remarks			
BUFF	1, 8	Bypassing via a ceramic capacitor is mandatory. Bridge #1 and #8			
GND	2, 5, 6, 13, 14, 15, 17 and bottom pad	It is important to ground the bottom pad (also called "thermal pad").			
INO	19				
IN1	20				
IN2	21	Sensor input. Connect one electrode of each touch sensor here, all			
IN3	22	the opposite electrodes in common to GND.			
IN4	23				
IN5	24				
OUTO	16				
OUT1	12	CMOS output which indicates touch sensor state :			
OUT2	11	'low' = touched			
OUT3	10	nign = untouchea or umea-out			
OUT4	9	OUT <i>n</i> corresponds to IN <i>n</i> for every <i>n</i> .			
OUT5	3				
VDD	4,18	Bypassing via a ceramic capacitor is mandatory. Bridge #4 and #18			

Leave unconnected pin 7 and amongst the IN and OUT ports those which remain unused.

### **PICO**CAP

#### 2.3.4 Recommended Schematics

Figure 2-3: Recommened Schematics









acam-messelectronic gmbh Am Hasenbiel 27 76297 Stutensee-Blankenloch Germany ph. +49 7244 7419 - 0 fax +49 7244 7419 - 29 e-mail: sales@acam.de www.acam.de